

3.2M
Effective
Pixels

ZOOM
3X Optical
3.2X Digital

DIGITAL CAMERA
FinePix A210

New



**High-performance digital photography
at its easiest and most convenient**

- ▶ **3.2 million effective pixels** for superb image quality
- ▶ **3X optical + 3.2X digital zoom**
- ▶ **Multi-language LCD display**
- ▶ **Low power consumption using two standard AA batteries**
- ▶ **Movie recording function**
- ▶ **Optional PictureCradle for easy link to any PC**



The FinePix A210: Serious digital performance is now a snap

Remarkable image quality

With 3.2 million effective pixels, the FinePix A210 delivers serious image quality. Details are sharp, colors are rich and brilliant. And its high-resolution image files make beautiful photo prints. There's never been an easier way to capture your memories in superb quality digital images.

High-performance zooming

The FinePix A210 features a high-performance Fujinon 3X optical zoom lens (equivalent to 36-108mm on a 35mm camera), making it easy to frame your subject perfectly. A smooth digital zoom function offers up to 3.2X* additional magnification.

* At 640 x 480-pixel mode

One-touch, fully automatic operation



Your new camera comes complete with batteries and a 16MB xD-Picture Card™, so you can start

taking pictures right away. Then just press the shutter button – and welcome to the world of digital photography. The FinePix A210 automatically controls focus, exposure, and white balance to give you great photos, first time and every time.

Low-power consumption

Thanks to its power-saving design, the FinePix A210 lets you take up to 300 shots* on a single pair of AA batteries.

* With the LCD turned off and using the flash for 50% of shots

Multi-language LCD display

All menus can be displayed in any of six languages: English, French, German, Spanish, Chinese, or Japanese. The easy-to-use LCD menus make it a breeze to change settings to your own personal preferences.

xD-Picture Card™ support

The FinePix A210 is designed around the ultra-compact xD-Picture Card™*. This versatile new memory card standard offers a number of advantages, including effortless PC data transfer with any compatible USB card reader or PC/CompactFlash™ card adapter.

* Supports card capacities of up to 512MB.

Optional PictureCradle

The PictureCradle, available separately, provides a simple and stylish way to automatically upload image files to your PC while simultaneously recharging the camera battery. Dedicated AC adapter and rechargeable battery are included with the PictureCradle.



With optional PictureCradle


Other features

- Movie recording function*
- Video output to a TV monitor
- Macro focus to 10cm

* Up to 60 seconds at 320 x 240 pixels

Specifications

DIGITAL CAMERA FinePix A210

| | | | | | | |
|--|---|-------------|------------|-----------|--------------------|--------------------|
| Number of effective pixels* | 3.2 million pixels | | | | | |
| CCD sensor | 1/2.7-inch CCD (Number of total pixels: 3.34 million pixels) | | | | | |
| Number of recorded pixels | Still image: 2048 x 1536 (3.15 million)/1600 x 1200/1280 x 960/640 x 480 pixels Movie: 320 x 240 pixels (10 frames/sec., without sound), 160 x 120 pixels (10 frames/sec., without sound) | | | | | |
| Storage media | xD-Picture Card™ (16MB to 512MB) | | | | | |
| File format | Still image: JPEG (Exif Ver. 2.2*)/Movie: AVI (Motion JPEG)  [Design rule for Camera File system compliant/DPOF-compatible] | | | | | |
| Number of images/recording time | The numbers of images and recording time will vary slightly depending on the type of subject. | | | | | |
| Modes | Still image | | | | Movie | |
| Image quality mode displayed | 3M | 2M | 1M | 0.3M | 320 | 160 |
| Number of recorded pixels | 2048 x 1536 | 1600 x 1200 | 1280 x 960 | 640 x 480 | 320 x 240 (10 fps) | 160 x 120 (10 fps) |
| DPC-16 (16MB) | 19 | 25 | 33 | 122 | Approx. 98 sec. | Approx. 5.6 min. |
| DPC-32 (32MB) | 40 | 50 | 68 | 247 | Approx. 199 sec. | Approx. 11.3 min. |
| DPC-64 (64MB) | 81 | 101 | 137 | 497 | Approx. 6.6 min. | Approx. 22.7 min. |
| DPC-128 (128MB) | 162 | 204 | 275 | 997 | Approx. 13.3 min. | Approx. 45.5 min. |
| DPC-256 (256MB) | 325 | 409 | 550 | 1,997 | Approx. 26.7 min. | Approx. 91.2 min. |
| DPC-512 (512MB) | 651 | 818 | 1,101 | 3,993 | Approx. 53.5 min. | Approx. 182.5 min. |
| Lens | Fujinon 3X optical zoom lens, F3.0 – F4.8 | | | | | |
| Lens focal length | Equivalent to 36 – 108mm on a 35mm camera | | | | | |
| Focus | Autofocus | | | | | |
| Focus distance | Normal: Approx. 80 cm/2.6 ft. to infinity Macro: Approx. 10 cm – 1.0 m/0.3 ft – 3.3 ft | | | | | |
| Aperture | F3.0/F7.0 (wide-angle) – F4.8/F10.8 (telephoto) | | | | | |
| Sensitivity | Equivalent to ISO 100 (at flash off) | | | | | |
| LCD monitor | 1.5-inch TFT (60,000 pixels) | | | | | |
| Flash | Automatic, 3.5m/11.5ft (max.) | | | | | |
| Terminal | Multiple connector (for USB 1.1 or optional PictureCradle), Video output socket | | | | | |
| Video output | NTSC/PAL selectable | | | | | |
| Power source | 2 AA Alkaline/Ni-MH battery or AC power adapter (optional) | | | | | |
| Dimensions | 98.5 (W) x 65.0 (H) x 52.5 (D) mm/3.9 (W) x 2.6 (H) x 2.1 (D) in. | | | | | |
| Weight | 175g/6.2oz. (excluding batteries and media) | | | | | |

xD-Picture Card™ and all other trademarks are the property of their respective holders.

| | |
|-----------------------------|---|
| Camera functions | |
| <i>Digital zoom</i> | 3.2X (640 x 480 pixels), 1.6X (1280 x 960 pixels), 1.28X (1600 x 1200 pixels) |
| <i>Shooting modes</i> | Auto, Manual |
| <i>Movie recording</i> | 320 x 240 pixels: 10 frames/sec., up to 60 sec. 160 x 120 pixels: 10 frames/sec., up to 240 sec. without sound, AVI format (Motion JPEG) Single frame (with 13X Playback zoom at 3M mode), 9 Multi-frame |
| <i>Playback</i> | 16 MB xD-Picture Card™ |
| Accessories included | 2 AA type alkaline batteries Hand strap USB cable Video cable Cradle adapter for FinePix A210 CD-ROM: USB driver, FinePix Viewer, ImageMixer VCD for FinePix |
| Optional accessories | xD-Picture Card™: DPC-16, DPC-32, DPC-64, DPC-128, DPC-256, DPC-512 AC Power Adapter AC-3V (Cannot be used as a battery charger for this model) PictureCradle CP-FXA10 (Includes AC-3VW and Rechargeable Battery NH-10, which can be charged only in this cradle) Battery Pack NH-10 (Can be charged with PictureCradle CP-FXA10) PC Card Adapter DPC-AD Image Memory Card Reader DPC-R1 CompactFlash™ Card Adapter DPC-CF Battery Charger with Battery BK-NH2/BK-NH Rechargeable Battery 2HR-3UF (2 Ni-MH batteries included) Soft Case SC-FX26 |

* Number of effective pixels: The number of pixels on the image sensor which receive input light through the optical lens, and which are effectively reflected in the final output data of the still image.

** Exif 2.2 is a newly revised digital camera file format that contains a variety of shooting information for optimal printing.



Windows® XP compatible

Specifications are subject to change without notice.

For more information on the full range of Fujifilm digital products, please visit our Website: <http://home.fujifilm.com>



FUJIFILM
FUJI PHOTO FILM CO., LTD.

26-30, NISHIAZABU 2-CHOME, MINATO-KU, TOKYO 106-8620, JAPAN

Ref. No. EB-307E (SK-03-06-DT-MW) Printed in Japan © 2003 Fuji Photo Film Co., Ltd.