

SUD

Design for You

Slim Body & Stylish Design

Available in a choice of silver or black, the slim, stylish FinePix J10 slips effortlessly into your purse or pocket and goes everywhere with ease.



Black

Silver

FINEPIX J10

SPECIFICATIONS

DIGITAL CAMERA FinePix J10

Number of effective pixels ^{#1}	8.2 million pixels
CCD sensor	1/2.5-inch
Storage media	Internal memory (Approx. 8MB) / xD-Picture Card™ (16MB - 2 GB) / SD / SDHC memory card ^{#2}
File format	Still image : JPEG (Exif Ver. 2.2) ^{#3} / Movie : AVI (Motion JPEG) [Design rule for Camera File system compliant / DPOF-compatible]
Number of recorded pixels	Still image: 3,264 × 2,448(8M) / 3,264 × 2,176(3 : 2) / 2,304 × 1,728 / 1,600 × 1,200 / 640 × 480
Lens	Fujinon 3x Optical zoom lens, F2.8 - F5.6
Lens focal length	f=6.2mm - 18.6mm, Equivalent to 35 - 113mm on a 35mm camera
Digital zoom	Approx. 5.1x
Aperture	F2.8 - F5.2 (Wide) / F5.6 - F10.4 (Telephoto)
Focus distance	Normal : Approx. 40cm / 1.3 ft. to infinity Macro : Wide angle : Approx. 15cm / 6 in. to 40cm / 1.3 ft. Telephoto angle : Approx. 40cm / 1.3 ft. to 80cm / 2.6 ft.
Sensitivity	AUTO / Equivalent to ISO 64 / 100 / 200 / 400 / 800 / 1600 (Standard Output Sensitivity)
Exposure control	TTL 64-zones metering
Exposure mode	Programmed AE
Shooting modes	Auto, Manual, Picture Stabilization (Anti-blur), Movie SP: Natural Light, Baby, Portrait, Landscape, Sport, Night, Beach, Snow, Fireworks, Sunset, Flower, Party, Museum, Text
Shutter speed	8 sec. to 1 / 2000 sec. (depends on exposure)
Continuous shooting	Top-3
Focus	Auto focus (Center)
White balance	Automatic scene recognition Preset (Fine, Shade, Fluorescent light (Daylight), Fluorescent light (Warm White), Fluorescent light (Cool White), Incandescent light)
Self-timer	Approx. 10 sec. / 2 sec. delay
Flash	Auto flash Flash modes : Auto, Red-eye Reduction, Forced Flash, Suppressed Flash, Slow Synchro
LCD monitor	2.5-inch, 153,000 dots , Amorphous silicon TFT color LCD monitor, Approx. 96% coverage
Movie recording	640 × 480, 320 × 240 pixels, 30 frames/sec. With monaural sound *Zoom function cannot be used during movie recording.
Photography functions	Best framing, Frame No. memory
Playback functions	Slide show, Trimming, Single frame, Multi-frame playback, Sorting by date, Image rotate
Video output	NTSC / PAL selectable
Digital input / output	USB
Power source	NP-45 Li-ion battery (included)
Dimensions	91.0 (W) × 55.0 (H) × 22.0 (D)* mm / 3.8 (W) × 2.2 (H) × 0.9 (D)* in. (excluding accessories and attachments) *Measures a mere 19.0mm/0.75 inches at its thinnest point.
Weight	Approx. 110g / 3.9 oz. (excluding accessories, batteries and memory card)
Accessories included	Li-ion battery NP-45, Battery charger BC-45A or BC-45, Hand strap, A/V cable, USB cable, CD-ROM : FinePixViewer-S / FinePixViewer, Owner's manual (CD-ROM), Basic manual
Optional accessories	xD-Picture Card™ : M 512MB, M 1GB, M 2GB Rechargeable battery NP-45, Battery charger BC-45, AC power adapter AC-5VX PC card adapter DPC-AD, Compact Flash™ card adapter DPC-CF

Guide to the number of available frames for battery operation

Battery	LCD monitor status	Number of frames
Li-ion battery NP-45	LCD monitor ON	Approx. 150 frames

According to the Camera & Imaging Products Association (CIPA) standards^{#4}: The battery (NP-45) is supplied with the camera.

^{#1} Number of effective pixels: The number of pixels on the image sensor which receive input light through the optical lens, and which are effectively reflected in the final output data of the still image.

^{#2} Please see the Fujifilm website to check memory card compatibility.

^{#3} Exif 2.2 is a newly revised digital camera file format that contains a variety of shooting information for optimal printing.

^{#4} CIPA DC-002-2003 "Standard Procedure for Measuring Digital Still Camera Battery Consumption" (extract) Pictures shall be taken at a temperature of 23°C, with the LCD monitor turned on, the zoom moved from full wide-angle to full telephoto (or vice-versa) and back again to its original position every 30 seconds, the flash used at full power every second shot and the camera turned off and on again once every 10 shots.



Microsoft, Windows, and Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries. Macintosh and Mac OS are trademarks of Apple Computer, Inc., registered in the U.S. and other countries. xD-Picture Card™, SD logo and all other trademarks are the property of their respective holders.

FUJIFILM
FUJIFILM Corporation

For more information, please visit our Website:
http://www.fujifilm.com/products/digital_cameras/index.html

Specifications are subject to change without notice.
All sample photos are simulated images.

Ref. No. EB-712E (SK · 08 · 01 · F1120 · F9711) Printed in Japan © 2008 FUJIFILM Corporation



FUJIFILM

FINEPIX J10

8.2 Megapixels | High Sensitivity ISO1600 | 19.0mm Slim Body

xD/SD Compatible Slot

Slim & Stylish,
Goes Everywhere With Ease



NEW



受注番号	得意先名	品名	色数	サイズ	目付・作業担当者				作業MAC	進行担当
					1	2	3	4		
32-1568962	(株)電通様	FinePix J10リーフ (英語)	4C	210mm 297mm	12/06	12/12	12/19	00/00	IS	伊藤

