

SPECIFICATIONS

FinePix Z200fd	
Number of effective pixels*1	10.0 million pixels
CCD sensor	1/2.3-inch CCD
Storage media	Internal memory (approx. 52MB) / xD-Picture Card™ (16MB - 2GB) / SD memory card / SDHC memory card*2
File format	Still image: JPEG (Exif Ver. 2.2**) Movie: AVI (Motion JPEG) with sound / Audio: WAVE format, Monaural sound (Design rule for Camera File system compliant / DPOF-compatible)
Number of recorded pixels	Still image: 3,648 × 2,736 (10M) / 3,648 × 2,432 (3:2 format) / 2,592 × 1,944 / 2,048 × 1,536 / 1,600 × 1,200 / 640 × 480
Lens	Fujinon 5x optical zoom lens, F3.8 - F4.8
Lens focal length	f=5.9 - 29.5 mm, equivalent to 33 - 165 mm on a 35 mm camera
Digital zoom	Approx. 5.7x
Aperture	Wide: F3.8 / F6.4, Telephoto: F4.8 / F8.0
Focus distance (from lens surface)	Normal: Wide: Approx. 60 cm / 2.0 ft. to infinity Telephoto: Approx. 1.0 m / 3.3 ft. to infinity Macro: Wide: Approx. 9 cm - 80 cm / 3.5 in. - 2.6 ft. Telephoto: Approx. 30 cm - 80 cm / 1.0 ft. - 2.6 ft.
Sensitivity	Auto / Equivalent to ISO 64 / 100 / 200 / 400 / 800 / 1600 (Standard Output Sensitivity)
Exposure control	TTL 256-zones metering
Exposure mode	Programmed AE
Shooting modes	Auto, Manual, Movie SP: Natural Light, Natural Light & with Flash, Portrait, Landscape, Sport, Night, Fireworks, Sunset, Snow, Beach, Underwater, Museum, Party, Flower, Text, Auction
Image stabilizer	CCD-shift type
Shutter speed	(Auto mode) 1/4 sec. to 1/1000 sec., (All other modes) 4sec. to 1/1000 sec.
Continuous shooting	1. Top-3 (max 0.6 frames/sec.) 2. Final-3 (max 0.6 frames/sec.) 3. Long-period (max 0.3 frames/sec.)
Focus	Auto focus (Center, Multi)
White balance	Automatic scene recognition Preset: Fine, Shade, Fluorescent light (Daylight), Fluorescent light (Warm white), Fluorescent light (Cool white), Incandescent light
Self-timer	Approx. 10 sec. / 2 sec. delay, Couple Timer, Group Timer
Flash	Auto flash Effective range (ISO AUTO): Wide: Approx. 70 cm - 3.6 m / 2.3 ft. - 11.8 ft. Telephoto: Approx. 70 cm - 2.9 m / 2.3 ft. - 9.5 ft. Macro: Approx. 30 cm - 80 cm / 1.0 ft. - 2.6 ft. Flash modes Red-eye removal OFF: Auto, Forced Flash, Suppressed Flash, Slow Synchro. Red-eye removal ON: Red-eye Reduction Auto, Red-eye Reduction & Forced Flash, Suppressed Flash, Red-eye Reduction & Slow Synchro.
LCD monitor	2.7-inch, Approx. 230,000 dots, amorphous silicon TFT color LCD monitor, Approx. 97% coverage
Movie recording	640 × 480 pixels / 320 × 240 pixels (30 frames/sec.) with monaural sound *Zoom function cannot be used during movie recording.
Photography functions	Face Detection (with Red-eye removal), High-speed shooting, Best framing, Frame no. memory, Silent mode
Ir communication	IrSimple™ / IrSS™
Playback functions	Face Detection, Slide show (with music), Scrap book view slide show, Trimming, Blog mode (with image processing function), Multi-frame playback including Micro Thumbnail mode, Sorting by date, Image rotate, Voice memo
Video output	NTSC / PAL selectable
Digital interface	USB 2.0 High-speed
Power supply	NP-45 Li-ion battery (included) / CP-45 with AC power adapter AC-5VX (sold separately)
Dimensions	92.0 (W) × 55.7 (H) × 20.0 (D) mm / 3.6 (W) × 2.2 (H) × 0.8 (D) in. (excluding accessories and attachments)
Weight	Approx. 134 g / 4.7 oz. (excluding accessories, battery and memory card)

Number of images / recording time

Mode	Still image							Movie	
	3,648 × 2,736	3,648 × 2,432 (3:2)	2,592 × 1,944	2,048 × 1,536	1,600 × 1,200	640 × 480	Movie recording time		
Quality	JPEG FINE	JPEG NORMAL	JPEG	JPEG	JPEG	JPEG	JPEG	VGA (30 fps)	QVGA (30 fps)
Internal memory (approx. 52MB)	10	21	24	41	65	81	333	58 sec.	1.5 min.
xD-Picture Card™	256MB	51	103	115	199	313	389	1,598	4.7 min.
	512MB	103	206	231	399	626	779	3,195	9.3 min.
	1GB	207	412	463	799	1,254	1,560	6,396	18.7 min.
	2GB	415	820	927	1,599	2,460	3,046	12,795	36.8 min.
SD memory card	512MB	100	199	224	386	606	754	3,094	9.0 min.
	1GB	201	399	449	774	1,215	1,511	6,196	18.1 min.
	2GB	402	795	898	1,550	2,385	2,953	12,402	35.6 min.
	4GB	805	1,591	1,798	3,102	4,773	5,909	24,820	71.3 min.*
SDHC memory card	1GB	1,617	3,192	3,609	6,225	9,578	11,858	49,806	143.0 min.*
	2GB								230.5 min.*

Actual number of frames and recording time varies depending on the types of memory card or shooting condition.

*A movie recording will stop automatically when the movie file size becomes approx. 2GB.

*1 : Number of effective pixels: The number of pixels on the image sensor which receive input light through the optical lens, and which are effectively reflected in the final output data of the still image.

*2 : Please see the Fujifilm website to check memory card compatibility.

*3 : Exif 2.2 is a newly revised digital camera file format that contains a variety of shooting information for optimal printing.

*4 : CIPA DC-002-2003 Standard Procedure for Measuring Digital Still Camera Battery Consumption (extract) Pictures shall be taken at a temperature of 23°C, with the LCD monitor turned on, the zoom moved from full wide-angle to full telephoto (or vice-versa) and back again to its original position every 30 seconds, the flash used at full power every second shot and the camera turned off and then on again once every 10 shots.

Microsoft, Windows, Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries. Macintosh and Mac OS are trademarks of Apple Computer, Inc., registered in the U.S. and other countries. SD logo is a trademark. All other trademarks are the property of their respective holders.

For more information, please visit our Website:
http://www.fujifilm.com/products/digital_cameras/index.html

OPTIONAL ACCESSORIES

Li-ion battery
NP-45



xD-Picture Card™

DPC-M256 (256MB)
DPC-M512 (512MB)
DPC-MP1GB (1GB)
DPC-MP2GB (2GB)

Waterproof case WP-FXZ100

PC card adapter DPC-AD

CompactFlash™ card adapter DPC-CF

AC power adapter AC-5VX

Battery charger BC-45

DC coupler CP-45

Accessory availability may vary by country.
Please check with your local Fujifilm representative to confirm product availability.

ACCESSORIES INCLUDED

- Li-ion battery NP-45
- Battery charger BC-45
- Hand strap
- USB cable for the FinePix Z200fd
- A/V cable for the FinePix Z200fd
- CD-ROM: FinePixViewer
- Owner's manual

Guide to the number of available frames for battery operation

Battery	LCD monitor status	Number of frames
NP-45	LCD monitor ON	Approx. 170 frames

The number of frames per charge will decrease in Quick AF.

According to the Camera & Imaging Products Association (CIPA) standards*4. The battery (NP-45) is supplied with the camera.



Specifications are subject to change without notice.

FUJIFILM

FINEPIX Z200 *fd*

NEW



Focus on your style.

FUJIFILM
FUJIFILM Corporation

■ 10.0 Megapixels

■ 5x Optical zoom

■ (()) Dual IS (Image stabilization)





Silver



Black



Quality & Style

10.0 Megapixels

The sleek, flat body conceals a full 10 megapixels of high-resolution imaging performance, giving you the flexibility to enlarge and crop your favorite pictures without sacrificing image quality.

5x Optical Zoom

A high-quality 5x optical zoom lets you capture the wide-angle view or move right in for high-impact close-ups.



Wide angle



5x zoom

High Sensitivity ISO1600

Indoors, at night, or in the midst of fast-moving action: high sensitivity (ISO 1600) makes it easy to take bright, clear photos regardless of the conditions.

Dual IS (Image Stabilization)

High Sensitivity + CCD Shift Image Stabilization

Dual Image Stabilization lets you say goodbye to blurry shots caused by camera shake or moving subjects. CCD shift image stabilization automatically calculates and compensates for camera shake, while high sensitivity boosts the shutter speed to freeze movement and preserve bright, sharp detail.



Conventional digital camera



FinePix Z200fd



Pink



Red & Black



Technology & Style

Face Detection

Face Detection gives you beautiful people pictures by identifying faces and adjusting focus and exposure to ensure bright, clear results. And automatic red-eye removal detects and compensates for unsightly red-eye in detected faces, for fail-safe flash photography in low light scenes.


Finds and focuses faces instantly!
Optimizes brightness
for exceptional results



FinePix Z200fd

Lost photo opportunity
Up to 10 faces detected almost instantly

Corrects "Red Eye" in detected
faces automatically




FinePix Z200fd

Lost photo opportunity

New Self-Timer Functions


Face Detection adds a new element of flexibility and fun to the familiar self-timer function: with the Face Detection Self Timer, the camera can detect the number and position of faces in a scene and snap the photo at the optimum moment, with all the faces in focus and properly exposed.

Couple Timer



Just the two of you? Couple Timer waits until two faces are close together in the frame. Select "Near," "Close-up" or "Super-Close" depending on the level of intimacy you're aiming for!

Group Timer




Out and about with your friends? Group Timer gives you time to get into position before taking that great commemorative photo. Settings can be selected for two, three or four people, depending on the number of friends you want to fit into the photo.

Usability & Style

Intelligent Flash

Intelligent Flash automatically calculates optimum flash output and sensitivity, capturing both the subject and the background in beautiful, natural detail.



Conventional digital camera

FinePix Z200fd

Natural Light & with Flash

This mode automatically captures the same scene twice, once at high sensitivity and natural light and once with Intelligent Flash. Both photos are then displayed side by side for quick comparison.




First shot Without flash (Natural Light)

Second shot With Intelligent Flash

Various Scene Positions

Select the Scene Position to match the situation and the camera does the rest, ensuring the ideal settings for everything from shutter speed and exposure to white balance.



Portrait

Flower

20.0mm Super Flat Body



Sliding Lens Shield

Micro Thumbnail View

Navigate, view, and select from up to 100 photos, displayed in a 10 x 10 array. The bright, high-resolution LCD makes it easy to identify images, even at micro-size.

2.7-inch LCD

The big, bright 2.7-inch LCD makes it a pleasure to compose and view photos. And with 230,000 dots, photo details are sharp and clear and on-screen menus easy to read.

Slide Show with Music

New in-camera slide show functions make slide shows easier to organize and give you entertaining ways to share those memorable moments. Now you can select music to create a soundtrack for your slide show and highlight your people pictures with powerful Face Detection functions.

Slide Show

Create entertaining personalized slide shows with close-ups of detected faces.




Scrap Book View

Enliven your slide shows with screens of multiple images, displayed in a stylish scrap book montage.



Auction mode

Combine several photos into a single image for effortless posting to auction sites.



Blog mode

Automatically resize photos for posting to a blog or other web page, eliminating the need for time-consuming PC-based editing and optimizing. Add an artistic touch to your pictures with easy-to-use image enhancement tools such as Illustration and Painting effect.

Versatility & Style

Folder Management

Preset folders let you save and organize your photos for quick retrieval or instant slide shows. Personal photos can be stored in a password-protected folder labeled "Private".



IrSimple™ for Wireless Communication

Share photos with other IrSimple-compatible cameras with no need for cables or connections. It's instant, effortless, and wireless!



xD/SD Compatible Slot

The versatile card slot is compatible with ultra compact xD-Picture Cards and both standard and high-capacity Secure Digital (SD) memory cards.

