

SERICOL
More than ink...Solutions.[™]
FUJIFILM



WIDE FORMAT MEDIA
Cost Saving, High Quality Roll Media

DESIGNED FOR
Solvent and UV Solutions



Fujifilm Graphic Systems is pleased to announce the introduction of Fujifilm Wide Format UV and Solvent roll media. The addition of this media complements FGSU's existing wide format portfolio that includes roll and flatbed printers, UV and solvent digital ink, color management RIP software and a full range of technical support, service and consulting will get you "in control" of your wide format solutions. The Fujifilm range of roll media will provide optimal performance in terms of print quality, color development while providing maximum durability and ease of use.

Our range of wide format media was specifically developed to provide optimal performance in terms of print quality, color development, maximum durability, ease-of-use and to keep our customer "in control" of their wide format needs.

The Fujifilm media will consist of:

- Banner Selections
- Adhesive Backed Vinyl
- Wall Graphic Media
- Backlit Media Selections
- Premium Papers
- Canvas Selections
- Perforated Window Film
- Specialty Indoor Graphics

Full Solution Provider now includes:

- Roll and flatbed printers
- UV and solvent digital ink
- Color management RIP software
- Full range of technical support, service and consulting
- Taskero Universe
- Wide Format Digital Media

THE FUJIFILM GREEN POLICY

We at Fujifilm believe that "sustainable development" of the Earth, mankind, and companies in the 21st century is an issue that must be addressed with the highest priority. As a socially responsible corporation, we actively undertake corporate activities with our environmental values in mind. We strive to be a dedicated steward of the environment and assist our customers and corporate partners in doing the same.



BANNER SELECTIONS

FUJIFILM 10 oz. Gloss Banner:

11 mil, bright white, smooth print surface. Use indoor or temporary outdoor (<54"). Can be sewn or heat sealed. Economically priced scrim available in 30", 38", 54", 63" x 164' rolls.

FUJIFILM 13 oz. Gloss Banner:

13 mil, bright white, high gloss finish with smooth print surface. Use indoor or temporary outdoor (<64"). Can be sewn or heat sealed. Economically priced scrim available in 38", 54" x 82' rolls; 38", 54", 63" x 164' rolls.

FUJIFILM 13 oz. Matte Banner:

14 mil, true matte finish, no glare, bright white. Use indoor or temporary outdoor (<54"). Can be sewn or heat sealed. Economically priced scrim available in 38", 54" x 82' rolls; 38", 54", 63" x 164' rolls.

FUJIFILM 13 oz. Premium Dura Gloss Banner:

16 mil, high gloss finish, super strong construction, bright white. Best choice for large outdoor graphics. Can be sewn or heat sealed. High tear strength, superb value. Available in 39", 54", 63" x 164' rolls.

FUJIFILM 13 oz. Premium Dura Matte Banner:

16 mil, matte finish, no glare. Super strong construction, bright white. Best choice for large outdoor graphics. Can be sewn or heat sealed. High tear strength, superb value. Available in 39", 54", 63" x 164' rolls.

FUJIFILM 13 oz. Two Sided Ultra Smooth Banner:

Two sided printing, smooth printing surface on both sides, flexible for folding. Super strong construction. Block-out, 100% opaque. Can be sewn or heat sealed. Available in 39", 54", 63" x 164' rolls.

PREMIUM PAPERS

FUJIFILM Premium Photo Satin Paper:

7 mil, resin coated photo quality with satin low glare finish. Works with heat or pressure over laminates. Smooth, blemish free coating. Available in 54", 60" x 150' rolls.

FUJIFILM Poster Paper:

9 mil, high grade poster paper with great color pop and photo realistic. High stiffness, high opacity, wet strength durable paper for indoor/outdoor use. Available in 30", 54", 63" x 165' rolls.

CANVAS SELECTIONS

FUJIFILM Artist Gloss Canvas Premium:

17 mil, gloss finish compatible with solvent ink. Waterfast, no edge cracking with uniform surface structure. Excellent flexibility for stretching. Fast dry time. Available in 36", 54", 60" x 50' rolls.

FUJIFILM Artist Matte Canvas:

24 mil, matte finish, compatible with solvent ink. 2:1 natural canvas structure. Waterfast, no edge cracking with uniform surface structure. Well suited for framing. Available in 56" x 150' rolls.

SPECIALTY INDOOR GRAPHICS

NEW!

FUJIFILM Floor Graphic w/ Overlaminates:

3.5mil gloss calendared vinyl base film with a low tach adhesive for easy installation and removal, 3.75mil UL approved slip resistant overlaminates; for short term, indoor usage on rigid surfaces such as hardwood, tile, and smooth concrete floors. Available in 54" x 100' rolls.

FUJIFILM Premium Wall Graphics:

12 mil, tear resistant polypropylene base, compatible with solvent inks. Water resistant, fast dry time, good lamination characteristics. Removable adhesive. Available in 36", 42", 50" x 100' rolls.

ADHESIVE BACKED VINYL

FUJIFILM Adhesive Gloss Vinyl:

3.5 mil, gloss calendared vinyl with permanent adhesive. 70 lbs. lay flat liner. Designed for temporary interior/exterior signage, decals, point of purchase displays. Available in 30", 54", 60" x 150' rolls.

NEW!

FUJIFILM Adhesive Matte Vinyl:

3.5 matte calendared vinyl with a permanent adhesive, grey adhesive to increase opaqueness. Designed for temporary indoor/exterior signage, decals, point of purchase displays. Available in 54", 60" x 150' rolls.

PERFORATED WINDOW FILM

FUJIFILM Window Perf Film:

10 oz/14 mil, bright white calendared 60/40 vinyl with black back. Hole size 1.6mm, transparency rate 40%. Clear acrylic adhesive, easy to apply. Available in 54" x 100' rolls.

FUJIFILM Non-adhesive Window Perf 70/30:

Bright white print side with a black on the reverse side of high contrast, 70% printable and 30% viewable through 1.5mm holes, uses FUJIFILM Removable adhesive with liner to stick to the inside of windows (8.9" x 100' rolls). Available in 54" x 100' rolls.

BACKLIT MEDIA

FUJIFILM Matte Backlight – 8.5 mil:

Front print, matte diffusion coating with long life UV durability. Print and post, no laminating required. Available in 36", 54", 60" x 100' rolls.

FUJIFILM Gloss Backlight:

Front print, gloss coating for a photo finish, front and backlight possible, scratch resistant. Available in 36", 54", 60" x 100' rolls.



SERICOL
More than ink...Solutions.
FUJIFILM